

Parameters	Model: RITMSCENAR Pro Prime C (SCENAR-1-NT version 01C)
Power supply	4 x AAA batteries
Maximum current consumption	650 mA or less
Stimuli frequency	15 Hz - 350 Hz
Display	Coloured LCD Matrix
Amplitude modulation (AM) settings	1:1; 2:1; 3:1; 4:1; 5:1; single burst of high intensity - 'BEE mode'
Frequency modulation (FM) mode variation	30-120 Hz frequency range with 7 sec cycle
Dosed modes	Dose 1 mode: integral dose and null Dose 2: differential dose
Screening modes	Dose 3, Dose 4 and Dose 5 (screening with a local electrode)
Damping modes	4 constant modes, 1 variable mode
Intensity (number of impulses in a burst)	1-8 impulses in a burst with a gap from 200 to 1600 μ s
Energy level tuning	1 - 250
Combined modulation mode	Sw1, Sw2, Sw3 and Sw4: pulse shape, gap between pulses and stimuli frequency simultaneously change in 4 different combinations; this also refers to the additional variation of the number of impulses in a burst
Factory/savable user presets:	28 / 5
Dimensions	190x70x40 mm
Weight	0.4 kg