

<b>Parameters</b>	<b>Model: RITMSCENAR Super Pro v.2 (SCENAR-1-NT version 01C)</b>
<b>Power supply</b>	4 x AAA batteries
<b>Maximum current consumption</b>	650 mA or less
<b>Stimuli frequency</b>	15 Hz - 350 Hz
<b>Display</b>	Coloured LCD Matrix
<b>Amplitude modulation (AM) settings</b>	1:1; 2:1; 3:1; 4:1; 5:1; single burst of high intensity - 'BEE mode'
<b>Frequency modulation (FM) mode variation</b>	30-120 Hz frequency range with 7 sec cycle
<b>Dosed modes</b>	Dose 1 mode: integral dose and null Dose 2: differential dose
<b>Screening modes</b>	Dose 3, Dose 4 and Dose 5 (screening with a local electrode)
<b>Damping modes</b>	4 constant modes, 1 variable mode
<b>Intensity (number of impulses in a burst)</b>	1-8 impulses in a burst with a gap from 200 to 1600 $\mu$ s
<b>Energy level tuning</b>	1 - 250
<b>Combined modulation mode</b>	Sw1, Sw2, Sw3 and Sw4: pulse shape, gap between pulses and stimuli frequency simultaneously change in 4 different combinations; this also refers to the additional variation of the number of impulses in a burst
<b>Factory/savable user presets:</b>	32 / 5
<b>Dimensions</b>	190x70x40 mm
<b>Weight</b>	0.4 kg